

**Date:** January 21, 2022

**Models Affected:** All Model Platforms Listed Above With Electric Start

**Serial Number**

**Range Affected:** Model Year 2022 Production

**Subject:** Battery Substitutions

INFORMATIONAL ONLY

**NOTE:** *These materials are prepared for use by trained technicians who are experienced in the service and repair of equipment of the kind described in this publication, and are not intended for use by untrained or inexperienced individuals. Such individuals should seek the assistance of an authorized service technician or dealer.*

**NOTE:** *Always wear eye protection while servicing equipment. Wear hearing protection when appropriate. Always work in a well ventilated area and follow all safety precautions when dealing with combustible materials.*

**NOTE:** *Left (LH) and Right (RH) sides are determined from the operator's position and facing in the forward direction.*

**PURPOSE:**

Due to supply chain challenges with batteries, units have the possibility of either having a traditional Lead Acid Wet Cell Battery (**725-1704A** or **725-1706B**) or one of three (3) AGM style batteries. This Advisory is to inform our Service Network of possible battery substitutions on Model Year 2022 platforms listed at the top of this page.

**ACTION REQUIRED:**

When performing Pre-Delivery set up or servicing Model Year 2022 product, be sure to identify what style battery is installed in the unit being prepped or serviced to insure the proper style charger is being used when charging the battery.

**NOTE:** *Make sure your current battery charger is compatible with AGM batteries.*

1. **725P17130** AGM Battery 230cca 16AHR (*Direct replacement of the 725-1707D*).
2. **725P17335** AGM Battery 210cca 11AHR (*Used in Riders and Zero Turn Riders*).
3. **725P17136** AGM Battery 135cca 7AHR (*Used in Model 700 Riders & Mini Riders*).

The **725P17335** & **725P17136** use different style hardware (*M6-1mm x 12mm HHCS & M6-1mm square nut*) to secure the positive and negative battery cables. The **725P17130**, uses the same hardware (*1/4-20 x 0.75 HHCS & 1/4-20 hex nut*) that the **725-1704A**, **725-1706B** & **725-1707D** have always used.

**NOTE:** *Hardware can be purchased by ordering 490-280-0019 which contains a quantity 2 each of the M6-1mm x 12mm HHCS & M6-1mm square nut and 2 each of the 1/4-20 x 0.75 HHCS & 1/4-20 hex nut.*



**FIGURE 1**

This Advisory is being released for informational purposes only.

SERVICE MANAGER	PARTS MANAGER	SALES MANAGER	SERVICE TECH.	SERVICE TECH.

Circulate and Initial